

MAXTECH

PNP 175X30-Ø8 HL44

EAN 4031582320602

Broj porudžbine 00005566



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	polipropilen
	mekan
materijal omotaca	Poliuretanski, penasti
Nošenje	precizini kuglicni lezaj
Boja Tocak	Crna
štيتnici omotaca	Sa threadguard
Prečnik	175 mm
Širina omotac	30 mm
dimenzija rupa osovina	8 mm
duzina glavcine	44 mm
Širina tela	30 mm
Teškoća gazećeg omotac (A)	70 Šešelj A

PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●●○

Ishrana ●●●○○

otpornost na rdju ●●●○○

OSNOVNI ATRIBUTI

Naziv proizvoda	Maxtech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	75 kg
Statički Nosivost	150 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,3 kg

MAXTECH

PNP 175X30-Ø8 HL44

EAN 4031582320602

Broj porudžbine 00005566



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

