

# NOVATECH

ETX082X70-Ø17 HL75-B

EAN 4031582331936



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Steel, iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing, sealed
Threadguards	With threadguard
Diameter	3.23 in
Tread width	2.76 in
Axle hole diameter	0.67 in
Hub length	2.95 in
Hardness of tread (A)	92 Shore A
Bearing type	6303
Sealing type	B
Suitable for	jungheinrich_mic

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Load capacity at 1.8 mph	1543.23 lb
Load capacity Static	3086.47 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	2.21 lb

# NOVATECH

ETX082X70-Ø17 HL75-B

EAN 4031582331936



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

