

ELASTECH

SEP 200x50-Ø20 HL60 plus

EAN 4031582346671



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOČAK

Tread hardness	mekan
Materijal za telo	Čelik od limova, težak
materijal omotaca	Elastična guma, crna, vulkanizovana
Nošenje	precizini kuglični ležaj
Boja Tocak	Crni mlaz (sličan RAL9005)
stitnici omotaca	Sa threadguard
Prečnik	200 mm
Širina omotac	50 mm
dimenzija rupa osovina	20 mm
dužina glavčine	60 mm
Širina tela	50 mm
Teškoća gazećeg omotac (A)	68 Šešelj A

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ● ● ●
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ● ●

OSNOVNI ATRIBUTI

Naziv proizvoda	Elastech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	600 kg
Nosivost na 6 km/h	500 kg
Električni provod	no
nerdjajući	no
Statički Nosivost	1000 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	85 °C
Ukupna težina	3.48 kg

ELASTECH


SEP 200x50-Ø20 HL60 plus

EAN 4031582346671

Broj porudžbine 00834217
Product Drawings



BETTER MOBILITY. BETTER LIFE.




ELASTECH

SEP 200x50-Ø40 HL60 plus

EAN 4031582346671

Broj porudžbine 008-217



BETTER MOBILITY. BETTER LIFE.