PRODUCT INFORMATION

AGILA TWIN

2975UAK050P30-11

EAN 4031582302820

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●●○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Agila twin
Type	Swivel castor with wheel brake
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	70 kg
Electric Conductive	No
Stainless	No
Load capacity Static	140 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall Height	69 mm
Overall width	57 mm
Overall weight	0.32 kg

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Twin wheel housing
Swivel Bearing	Two ball races
Housing Color	Blue passivated
Offset	25 mm
Swivel radius	77 mm
Swivel interference	155 mm
Dome diameter	53 mm

WHEEL

Body material	Polyamide
Tread Material Mix	Polyurethane, injected
Bearing	Cone ball bearing
Wheel Color	Slate grey (RAL7015)
Threadguards	With threadguard
Diameter	50 mm
Tread width	20 mm
Body width	20 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

FITTING

Fitting type	Bolt hole
Bolt hole diameter	11 mm

© Copyright 2026 TENTE International GmbH

AGILA TWIN

2975UAK050P30-11

EAN 4031582302820

Order number 00030578

Product Drawings



