

ALPHA

3470UOR200P30-13

EAN 4031582441444



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Alpha
Housing type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	200 kg
Load capacity Static	400 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	235 mm
Overall weight	2.047 kg

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Roller bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	200 mm
Tread width	50 mm
Hardness of tread (D)	75 Shore D

HOUSING

Material fork	Steel sheet, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Offset	55 mm
Swivel radius	155 mm
Swivel interference	310 mm

FITTING

Fitting type	Bolt hole
Bolt hole diameter	13 mm

ALPHA

3470UOR200P30-13

EAN 4031582441444



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

