

PRODUCT INFORMATION

# DURATECH

UOP100x36-Ø8 HL45

EAN 4031582442809



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polyamide
Tread Material Mix	Identical with wheel body
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	100 mm
Tread width	36 mm
Axle Hole Diameter	8 mm
Hub Length	45 mm
Hardness of tread (D)	75 Shore D

## PERFORMANCE

Roll Performance	● ● ● ● ●
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion Resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product Name	Duratech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	250 kg
Electric Conductive	No
Stainless	No
Load capacity Static	500 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.25 kg

# DURATECH

UOP100x36-Ø8 HL45

EAN 4031582442809



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

