

# DELTA TWIN

9948IEP125P63

EAN 4031582365825  
Order number 00837805



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Delta twin
Housing type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	600 kg
Load capacity at 6 km/h	480 kg
Load capacity Static	1200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall height	178 mm
Overall width	157 mm
Overall weight	3.921 kg

## WHEEL

Body material	Aluminium
Tread material	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Black
Threadguards	Without threadguard
Diameter	125 mm
Tread width	50 mm
Body width	50 mm
Hardness of tread (A)	68 Shore A

## HOUSING

Material	Iron forged, heavy
Fork shape	Twin wheel housing
Colour	Transparent coating
Dome diameter	136 mm

## FITTING

Fitting type	Rectangular plate
Plate length	137 mm
Plate width	137 mm
Plate hole length (Minimum)	75 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Minimum)	105 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	11 mm

# DELTA TWIN

9948IEP125P63

EAN 4031582365825  
Order number 00837805



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

