

FOOTMASTER

FOOT MASTER GDN- 40-F-NYN

EAN 4031582413120



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	○ ○ ○ ○ ○
Movement Noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion Resistance	○ ○ ○ ○ ○

CORE ATTRIBUTES

Product Name	Footmaster
Type	Swivel castor
Load capacity at 3 km/h	50 kg
Electric Conductive	No
Stainless	No
Load capacity Static	50 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	90 °C
Overall Height	71 mm
Overall width	57 mm
Overall weight	0.32 kg

HOUSING

Housing Color	White
Offset	30 mm
Swivel radius	51 mm
Swivel interference	102 mm
Dome diameter	57 mm

WHEEL

Bearing	Roller bearing, damped
Wheel Color	Black
Diameter	42 mm
Tread width	19 mm
Body width	19 mm

FITTING

Plate length	55 mm
Plate width	55 mm
Plate hole length (Maximum)	42 mm
Plate hole width (Maximum)	42 mm
Plate hole diameter	6.5 mm

FOOTMASTER

FOOT MASTER GDN- 40-F-NYN

EAN 4031582413120

Order number 00062074
Product Drawings



BETTER MOBILITY. BETTER LIFE.

