

ALPHA SMART

3377DVR200P63

EAN 4031582331646
Order number 00035056



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

CORE ATTRIBUTES

Product name	Alpha smart
Type	Swivel castor with total lock
Load capacity at 3 km/h	205 kg
Load capacity at 4 km/h	205 kg
Load capacity Static	410 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	240 mm
Overall weight	3.202 kg

WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, black
Bearing	Roller bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	200 mm
Tread width	30 mm
Hardness of tread (A)	85 Shore A

HOUSING

Material fork	Steel sheet, heavy
Fork shape	Slim
Swivel bearing	Two ball races
Offset	52.5 mm
Swivel radius	164.5 mm
Swivel interference	329 mm

FITTING

Fitting type	Medium rectangular plate
Plate length	137 mm
Plate width	105 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Minimum)	77 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm

ALPHA SMART

3377DVR200P63

EAN 4031582331646
Order number 00035056



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

