

PRODUCT INFORMATION

MAXTECH

DNP400x90-Ø10 NL129 yellow with axle

EAN 4031582438208



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Load capacity at 1.8 mph	319.67 lb
Electric conductive	no
Stainless	no
Load capacity Static	418.88 lb
Overall weight	7.98 lb



BETTER MOBILITY. BETTER LIFE.

WHEEL

Body material	Sheet Steel
Tread material	Polyurethane, foamed
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	15.75 in
Tread width	3.54 in
Axle hole diameter	0.39 in
Hub length	5.08 in

MAXTECH

DNP400x90-Ø10 NL129 yellow with axle

EAN 4031582438208



BETTER MOBILITY. BETTER LIFE.

Product Drawings

