

PURETECH

PIR 200X50-Ø20

EAN 4031582320381
Order number 00050619



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Solid rubber, non-marking
Bearing	Roller bearing
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	7.87 in
Tread width	1.97 in
Axle hole diameter	0.79 in
Hub length	2.36 in
Body width	1.97 in
Hardness of tread (A)	80 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	451.95 lb
Load capacity Static	903.89 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	3.39 lb

PRODUCT INFORMATION

PURETECH

PIR 200X50-Ø20

EAN 4031582320381
Order number 00050619



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

