

ALPHA

3470UOO160P30-13

EAN 4031582304671
Broj porudžbine 00032792

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Alpha
Tip kućišta	Okretanje Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	200 kg
Statički Nosivost	400 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Sveukupna visina	195 mm
Ukupna težina	1,633 kg

TOCAK

Materijal za telo	poliamid
materijal omotaca	Identično sa telom Tocak
Nošenje	klizni lezaj
osovina	Završena sa navrtkom
stitnici omotaca	Bez stražara
Prečnik	160 mm
Širina omotac	40 mm
Teškoća gazećeg omotac (D)	75 Šor D

KUCISTE

Materijal	Čelični list, težak
oblik viljuska	siroko
okretni lezaj	Dve lopte
ofset	55 mm
okretni radijus	135 mm
Otpor okretanju	270 mm

PRILAGOĐAVANJE

Tip uklapanja	otvor za vijak
dimenzija rupa sraf	13 mm

ALPHA

3470UOO160P30-13

EAN 4031582304671
Broj porudžbine 00032792



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

