

PRODUCT INFORMATION

DURATECH HEAT

BOG 080x35 HL45,5 asm.

EAN 4031582317695



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ○ ○ ○ |
| Attrition            | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ● ● |

CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Duratech heat                 |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph    | 220.46 lb                     |
| Electric conductive         | no                            |
| Stainless                   | Yes                           |
| Load capacity Static        | 440.92 lb                     |
| Temperature range (Minimum) | -40 °F                        |
| Temperature range (Maximum) | 536 °F                        |
| Overall weight              | 0.46 lb                       |

WHEEL

|                       |                                   |
|-----------------------|-----------------------------------|
| Body material         | Plastic thermoset, heat-resistant |
| Tread material        | Identical with wheel body         |
| Bearing               | Dry bearing bush                  |
| Wheel color           | Black                             |
| Diameter              | 3.15 in                           |
| Tread width           | 1.38 in                           |
| Axle hole diameter    | 0.31 in                           |
| Hub length            | 1.79 in                           |
| Body width            | 1.38 in                           |
| Hardness of tread (D) | 90 Shore D                        |

# DURATECH HEAT

BOG 080x35 HL45,5 asm.

EAN 4031582317695

Order number 00035369

Product Drawings



BETTER MOBILITY. BETTER LIFE.

