PRODUCT INFORMATION

DURATECH HEAT

BOG 080x35 HL45,5 asm.

EAN 4031582317695



Image may differ from the original product

WHEEL

Body material	Plastic thermoset, heat-resistant
Tread material	Identical with wheel body
Bearing	Dry bearing bush
Wheel color	Black
Diameter	3.15 in
Tread width	1.38 in
Axle hole diameter	0.31 in
Hub length	1.79 in
Body width	1.38 in
Hardness of tread (D)	90 Shore D

PERFORMANCE

Roll Performance	●●●○○
Movement noise	●●○○○
Attrition	●●●●●
Corrosion resistance	●●●●●

CORE ATTRIBUTES

Product name	Duratech heat
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	220.46 lb
Electric conductive	no
Stainless	Yes
Load capacity Static	440.92 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	536 °F
Overall weight	0.46 lb

© Copyright 2026 TENTE International GmbH


DURATECH HEAT

BOG 080x35 HL45,5 asm.

EAN 4031582317695

Order number 00035369

Product Drawings



© Copyright 2026 TENTE International GmbH