PRODUCT INFORMATION

# AGILA TWIN

2975UAP050P40

EAN 4031582439526



Image may differ from the original product

## PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement noise | ●●●○○ |
| Attrition | ●●●●○ |
| Corrosion resistance | ●●●○○ |

## CORE ATTRIBUTES

| | |
|---|---|
| Product name | Agila twin |
| Type | Swivel caster with wheel brake |
| Standard | EN12530 - Devices Castors |
| Load capacity at 1.8 mph | 154.32 lb |
| Electric conductive | no |
| Stainless | no |
| Load capacity Static | 308.65 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall height | 2.72 in |
| Overall weight | 0.65 lb |

## HOUSING

| | |
|---|---|
| Housing Material | Steel sheet, medium |
| Fork shape | Twin wheel housing |
| Swivel bearing | Two ball races |
| Offset | 0.98 in |
| Swivel radius | 3.03 in |
| Swivel interference | 6.1 in |

## WHEEL

| | |
|---|---|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 1.97 in |
| Tread width | 0.75 in |
| Hardness of tread (A) | 92 Shore A |

## FITTING

| | |
|---|---|
| Fitting type | Square plate |
| Plate length | 2.36 in |
| Plate width | 2.36 in |
| Plate hole length (Minimum) | 1.5 in |
| Plate hole length (Maximum) | 1.89 in |
| Plate hole width (Minimum) | 1.5 in |
| Plate hole width (Maximum) | 1.89 in |
| Plate hole diameter | 0.25 in |

© Copyright 2026 TENTE International GmbH


# AGILA TWIN


2975UAP050P40


EAN 4031582439526

BETTER MOBILITY. BETTER LIFE.

## Product Drawings






© Copyright 2026 TENTE International GmbH