

## GALEA STAINLESS

5081PJM100P30-10

EAN 4031582383393



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                                     |
|-----------------------------|-------------------------------------|
| Product name                | Galea stainless                     |
| Housing type                | Swivel castor with directional lock |
| Standard                    | EN12530 - Devices Castors           |
| Load capacity at 3 km/h     | 100 kg                              |
| Load capacity Static        | 200 kg                              |
| Temperature range (Minimum) | -20 °C                              |
| Temperature range (Maximum) | 60 °C                               |
| Overall height              | 139 mm                              |
| Overall width               | 66 mm                               |
| Overall weight              | 0.458 kg                            |

## WHEEL

|                       |                          |
|-----------------------|--------------------------|
| Body material         | Polypropylene            |
| Tread material        | Thermoplastic rubber     |
| Bearing               | Plain bearing, stainless |
| Threadguards          | With threadguard         |
| Diameter              | 100 mm                   |
| Tread width           | 30 mm                    |
| Hardness of tread (A) | 87 Shore A               |

## HOUSING

|                     |                                         |
|---------------------|-----------------------------------------|
| Material fork       | Polyamide                               |
| Fork shape          | Closed                                  |
| Swivel bearing      | Two ball races, reinforced or stainless |
| Offset              | 40 mm                                   |
| Swivel radius       | 128 mm                                  |
| Swivel interference | 256 mm                                  |
| Dome diameter       | 59 mm                                   |
| Stainless           | ✓                                       |

## FITTING

|                    |           |
|--------------------|-----------|
| Fitting type       | Bolt hole |
| Bolt hole diameter | 10 mm     |

# GALEA STAINLESS

5081PJM100P30-10

EAN 4031582383393



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

