

ELASTECH

EEZ 200X75-Ø100 DG

EAN 4031582318333

Broj porudžbine 00830872



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Čelik, gvožđe
materijal omotaca	Elastična guma, crna, vulkanizovana
Nošenje	Borehole, neobrađen
Boja Tocak	Crni mlaz (sličan RAL9005)
Prečnik	200 mm
Širina omotac	75 mm
dimenzija rupa osovina	100 mm
dužina glavcine	75 mm
Širina tela	75 mm
Teškoća gazećeg omotac (A)	68 Šešelj A

PERFORMANSE

Performanse kotrljanja	● ● ○ ○ ○
Buka u pokretu	● ● ● ● ●
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Elastech
Tip kućišta	Tocak
Standard	EN12533 - Tockovi za teske terete
Nosivost na 4 km/h	600 kg
Nosivost na 6 km/h	500 kg
Statički Nosivost	1000 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	85 °C
Ukupna težina	2,306 kg

ELASTECH

EEZ 200X75-Ø100 DG

EAN 4031582318333
Broj porudžbine 00830872



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

