

PRODUCT INFORMATION

DURATECH

UOR160x40-Ø20 HL58

EAN 4031582442786



Image may differ from the original product

PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Duratech                      |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph    | 881.85 lb                     |
| Electric conductive         | no                            |
| Stainless                   | no                            |
| Load capacity Static        | 1763.7 lb                     |
| Temperature range (Minimum) | -13 °F                        |
| Temperature range (Maximum) | 176 °F                        |
| Overall weight              | 1.27 lb                       |



BETTER MOBILITY. BETTER LIFE.

WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Polyamide                 |
| Tread material        | Identical with wheel body |
| Bearing               | Roller bearing            |
| Threadguards          | Without threadguard       |
| Diameter              | 6.3 in                    |
| Tread width           | 1.57 in                   |
| Axle hole diameter    | 0.79 in                   |
| Hub length            | 2.28 in                   |
| Hardness of tread (D) | 75 Shore D                |

# DURATECH

UOR160x40-Ø20 HL58

EAN 4031582442786



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

