

# ALPHA

3477PVO100P62

EAN 4031582305609



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Alpha                         |
| Type                        | Swivel caster with total lock |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph    | 165.35 lb                     |
| Electric conductive         | no                            |
| Stainless                   | no                            |
| Load capacity Static        | 330.69 lb                     |
| Temperature range (Minimum) | -4 °F                         |
| Temperature range (Maximum) | 140 °F                        |
| Overall height              | 5.04 in                       |
| Overall width               | 2.95 in                       |
| Overall weight              | 2.03 lb                       |

## HOUSING

|                     |                    |
|---------------------|--------------------|
| Housing Material    | Steel sheet, heavy |
| Fork shape          | Broad              |
| Swivel bearing      | Two ball races     |
| Housing Color       | Blue passivated    |
| Offset              | 1.61 in            |
| Swivel radius       | 4.84 in            |
| Swivel interference | 9.69 in            |
| Dome diameter       | 2.95 in            |

## WHEEL

|                       |                          |
|-----------------------|--------------------------|
| Body material         | Polypropylene            |
| Tread material        | Solid rubber, black      |
| Bearing               | Plain bearing            |
| Axle                  | Screwed with nut         |
| Wheel color           | Graphite black (RAL9011) |
| Threadguards          | Without threadguard      |
| Diameter              | 3.94 in                  |
| Tread width           | 1.38 in                  |
| Body width            | 1.38 in                  |
| Hardness of tread (A) | 80 Shore A               |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 4.13 in           |
| Plate width                 | 3.15 in           |
| Plate hole length (Minimum) | 3.03 in           |
| Plate hole length (Maximum) | 2.36 in           |
| Plate hole width (Minimum)  | 3.03 in           |
| Plate hole width (Maximum)  | 3.15 in           |
| Plate hole diameter         | 0.35 in           |

# ALPHA

3477PVO100P62



EAN 4031582305609

Order number 00004012  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

3477U00100P62-neu



Platte 3470-080P62-105x80

