

# BASETECH

POO100X36-Ø12

EAN 4031582418989



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Basetech                      |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 160 kg                        |
| Load capacity Static        | 320 kg                        |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 60 °C                         |
| Overall weight              | 0.105 kg                      |

## WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Polypropylene             |
| Tread material        | Identical with wheel body |
| Bearing               | Plain bearing             |
| Threadguards          | Without threadguard       |
| Diameter              | 100 mm                    |
| Tread width           | 36 mm                     |
| Axle hole diameter    | 12 mm                     |
| Hub length            | 44.4 mm                   |
| Hardness of tread (D) | 65 Shore D                |

# BASETECH

POO100X36-Ø12

EAN 4031582418989



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

