

# STEM

B40 - 11x20 / 10

EAN 4031582418002



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## FITTING

Fitting type	Stem with synthetic circlip, with collar
Stem diameter	11 mm

## PERFORMANCE

Corrosion Resistance ● ● ● ○ ○

## CORE ATTRIBUTES

Product Name	Stem
Type	Accessory
Load capacity at 3 km/h	60 kg
Electric Conductive	No
Stainless	No
Load capacity Static	120 kg
Overall Height	4.5 mm
Overall weight	0.04 kg