

STEM

B40 - 11x20 / 10

EAN 4031582418002



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Corrosion Resistance ● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Stem
Type	Accessory
Load capacity at 3 km/h	60 kg
Electric Conductive	No
Stainless	No
Load capacity Static	120 kg
Overall Height	4.5 mm
Overall weight	0.04 kg

FITTING

Fitting type	Stem with synthetic circlip, with collar
Stem diameter	11 mm