

PRODUCT INFORMATION

PURETECH

PVO200x50-Ø20 HL58

EAN 4031582442373



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ○ ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ○ ○ ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Puretech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	205 kg
Electric Conductive	No
Stainless	No
Load capacity Static	410 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	1.37 kg

WHEEL

Body material	Polypropylene
Tread Material Mix	Solid rubber, black
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	200 mm
Tread width	50 mm
Axle Hole Diameter	20 mm
Hub Length	58 mm
Hardness of tread (A)	85 Shore A

PURETECH

PVO200x50-Ø20 HL58

EAN 4031582442373



BETTER MOBILITY. BETTER LIFE.

Product Drawings

