PRODUCT INFORMATION

MONO

5025PJH080L51-10 RAL7035 regular brake

EAN 4031582460599



Image may differ from the original product

CORE ATTRIBUTES

Product Name	Mono
Type	Swivel castor with wheel brake
Load capacity at 3 km/h	70 kg
Electric Conductive	No
Stainless	No
Load capacity Static	140 kg
Overall Height	104 mm
Overall weight	0 kg

HOUSING

Housing Material	Polyamide
Fork shape	Closed
Swivel Bearing	Stem, swiveling
Housing Color	Light grey (RAL7035)
Offset	34 mm
Swivel interference	148 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Plain bearing
Threadguards	With threadguard
Diameter	80 mm
Tread width	24 mm
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	10 mm

© Copyright 2026 TENTE International GmbH


MONO

5025PJH080L51-10 RAL7035 regular brake

EAN 4031582460599

BETTER MOBILITY. BETTER LIFE.

Product Drawings



© Copyright 2026 TENTE International GmbH