

# MAXTECH

PNR389X85-Ø25 HL74 TFR

EAN 4031582400359



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polypropylene
Tread material	Polyurethane, foamed
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	389 mm
Tread width	85 mm
Axle hole diameter	25 mm
Hub length	74 mm

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Maxtech
Housing type	Wheel
Load capacity at 3 km/h	75 kg
Load capacity Static	150 kg
Overall weight	1.95 kg

# MAXTECH

PNR389X85-Ø25 HL74 TFR

EAN 4031582400359



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

