PRODUCT INFORMATION

# AGILA

## 2471PJP125R05-28 2.0 M8/19

EAN 4031582301441



Image may differ from the original product

### PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement noise | ●●●●○ |
| Attrition | ●●●○○ |
| Corrosion resistance | ●●●○○ |

### CORE ATTRIBUTES

| | |
|---|---|
| Product name | Agila |
| Type | Swivel caster with directional lock |
| Standard | EN12530 - Devices Castors |
| Load capacity at 1.8 mph | 220.46 lb |
| Electric conductive | no |
| Stainless | no |
| Load capacity Static | 440.92 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall height | 6.3 in |
| Overall width | 2.36 in |
| Overall weight | 2.41 lb |

### HOUSING

| | |
|---|---|
| Housing Material | Steel sheet, medium |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Housing Color | Blue passivated |
| Offset | 1.61 in |
| Swivel radius | 5.16 in |
| Swivel interference | 10.31 in |
| Dome diameter | 2.36 in |

### WHEEL

| | |
|---|---|
| Body material | Polypropylene |
| Tread material | Thermoplastic rubber |
| Bearing | Precision ball bearing |
| Wheel color | Silver gray (RAL7001) |
| Threadguards | With threadguard |
| Diameter | 4.92 in |
| Tread width | 1.26 in |
| Body width | 1.26 in |
| Hardness of tread (A) | 83 Shore A |

### FITTING

| | |
|---|---|
| Fitting type | Solid stem, round |
| Bolt diameter | 1.1 in |
| Bolt length | 1.77 in |
| Bolt thread position | 0.75 in |
| Bolt mounting holes quantity | 2 |

© Copyright 2026 TENTE International GmbH


# AGILA


2471PJP125R05-28 2.0 M8/19

EAN 4031582301441

Order number 00065500

**Product Drawings**



© Copyright 2026 TENTE International GmbH