

# KAPPA LOAD

9658FTP300P64

EAN 4031582316346



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement Noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                              |
|-----------------------------|------------------------------|
| Product Name                | Kappa load                   |
| Type                        | Fixed castor                 |
| Standard                    | EN12533 - Heavy Duty Castors |
| Load capacity at 4 km/h     | 2400 kg                      |
| Load capacity at 6 km/h     | 2000 kg                      |
| Electric Conductive         | No                           |
| Stainless                   | No                           |
| Load capacity Static        | 4800 kg                      |
| Temperature range (Minimum) | -20 °C                       |
| Temperature range (Maximum) | 60 °C                        |
| Overall Height              | 355 mm                       |
| Overall weight              | 17.23 kg                     |

## HOUSING

|                    |                    |
|--------------------|--------------------|
| Housing Material   | Iron forged, heavy |
| Fork shape         | Broad, reinforced  |
| Lubrication nipple | 1                  |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Cast iron              |
| Tread Material Mix    | Polyurethane, casted   |
| Bearing               | Precision ball bearing |
| Axle                  | Screwed with nut       |
| Threadguards          | With threadguard       |
| Diameter              | 300 mm                 |
| Tread width           | 80 mm                  |
| Hardness of tread (A) | 92 Shore A             |

## FITTING

|                             |                         |
|-----------------------------|-------------------------|
| Fitting type                | Large rectangular plate |
| Plate length                | 175 mm                  |
| Plate width                 | 140 mm                  |
| Plate hole length (Maximum) | 140 mm                  |
| Plate hole width (Maximum)  | 105 mm                  |
| Plate hole diameter         | 15 mm                   |

# KAPPA LOAD

9658FTP300P64

EAN 4031582316346

Order number 00801481

Product Drawings



BETTER MOBILITY. BETTER LIFE.

