

PRODUCT INFORMATION

ELASTECH

UFR100x34-Ø12 HL44,4 AZUL

EAN 4031582452891



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	160 kg
Electric Conductive	No
Stainless	No
Load capacity Static	320 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall weight	0.25 kg

WHEEL

Tread hardness	soft
Body material	Polyamide
Tread Material Mix	Elastic tire, non-marking, vulcanized
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	100 mm
Tread width	34 mm
Axle Hole Diameter	12 mm
Hub Length	44.4 mm
Hardness of tread (A)	64 Shore A

