

PURETECH AIR

DPP400x100-Ø20 HL74 2PR

EAN 4031582317817



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Puretech air
Tip	Tocak
Nosivost na 3 km/h	200 kg
Električni provod	no
nerdjajuci	no
Statički Nosivost	400 kg
Ukupna težina	2.46 kg

TOCAK

Tread hardness	mekan
Materijal za telo	Čelik lista
materijal omotaca	Pneumatička guma, profil linije
Nošenje	precizini kuglicni lezaj
stitnici omotaca	Sa threadguard
Prečnik	400 mm
Širina omotac	100 mm
dimenzija rupa osovina	20 mm
dužina glavcine	74 mm
Teškoća gazećeg omotac (A)	55 Šor A

PURETECH AIR

DPP400x100-Ø20 HL74 2PR

EAN 4031582317817



BETTER MOBILITY. BETTER LIFE.

Product Drawings

