

DURATECH SILENT

HUR125X36-Ø12 WHITE

EAN 4031582400694



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Vlažnost, hibridni materijal
materijal omotaca	poliamid
Nošenje	kotrljajući lezaj
štitnici omotaca	Bez stražara
Prečnik	125 mm
Širina omotac	36 mm
dimenzija rupa osovina	12 mm
dužina glavčine	44 mm
Teškoća gazećeg omotac (D)	75 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ● ●
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech silent
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	200 kg
Statički Nosivost	400 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,553 kg

DURATECH SILENT

HUR125X36-Ø12 WHITE

EAN 4031582400694



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

