

PRODUCT INFORMATION

PURETECH

PIR 160x40-Ø20

EAN 4031582320374



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polypropylene |
| Tread Material Mix | Solid rubber, non-marking |
| Bearing | Roller bearing |
| Wheel Color | Graphite black (RAL9011) |
| Threadguards | Without threadguard |
| Diameter | 160 mm |
| Tread width | 40 mm |
| Axle Hole Diameter | 20 mm |
| Hub Length | 58 mm |
| Body width | 40 mm |
| Hardness of tread (A) | 80 Shore A |

PERFORMANCE

| | |
|----------------------|-------------|
| Roll Performance | ● ● ● ○ ○ |
| Movement Noise | ● ● ● ● ○ |
| Attrition | ● ● ● ● ○ ○ |
| Corrosion Resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product Name | Puretech |
| Type | Wheel |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 135 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 270 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall weight | 0.85 kg |

PURETECH

PIR 160x40-Ø20

EAN 4031582320374

Order number 00023493
Product Drawings



BETTER MOBILITY. BETTER LIFE.

