

# ALPHA STAINLESS

8478UAO125P63 BURDEOS

EAN 4031582441833



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Alpha stainless
Housing type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	661.39 lb
Load capacity Static	1322.77 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall height	6.34 in
Overall weight	3.06 lb

## WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Plain bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	4.92 in
Tread width	1.57 in
Hardness of tread (D)	60 Shore D

## HOUSING

Material	Stainless steel, heavy
Fork shape	Broad
Stainless	✓

## FITTING

Fitting type	Rectangular plate
Plate length	5.39 in
Plate width	4.53 in
Plate hole length (Maximum)	4.13 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	3.15 in
Plate hole diameter	0.43 in

# ALPHA STAINLESS


8478UAO125P63 BURDEOS

EAN 4031582441833



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS



8478UAD125 P63

