

ZETA STAINLESS

8677UFX160P63

EAN 4031582313819
Order number 00829497



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Zeta stainless
Type	Swivel castor with total lock
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	300 kg
Load capacity at 6 km/h	240 kg
Stainless	✓
Load capacity Static	600 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall height	200 mm
Overall width	96 mm
Overall weight	3.205 kg

WHEEL

Body material	Polyamide
Tread hardness	soft
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing, sealed
Axle	Screwed with nut
Wheel color	Grey / non marking
Threadguards	With threadguard
Diameter	160 mm
Tread width	46 mm
Body width	46 mm
Hardness of tread (A)	64 Shore A

HOUSING

Material fork	Stainless steel, heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races
Colour	Stainless steel
Offset	55 mm
Swivel radius	161 mm
Swivel interference	322 mm
Dome diameter	96 mm

FITTING

Fitting type	Medium rectangular plate
Plate length	137 mm
Plate width	105 mm
Plate hole length (Minimum)	74 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Minimum)	74 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	11 mm

ZETA STAINLESS

8677UFX160P63

EAN 4031582313819
Order number 00829497



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

