

# DURATECH

TOP082X88-Ø20 HL90

EAN 4031582322613

Broj porudžbine 00804433



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

|                            |                          |
|----------------------------|--------------------------|
| Materijal za telo          | poliamid težak           |
| materijal omotaca          | Identično sa telom Tocak |
| Nošenje                    | precizini kuglicni lezaj |
| stitnici omotaca           | Bez stražara             |
| Prečnik                    | 82 mm                    |
| Širina omotac              | 88 mm                    |
| dimenzija rupa osovina     | 20 mm                    |
| dužina glavcine            | 90 mm                    |
| Teškoća gazećeg omotac (D) | 75 Šor D                 |
| Tip ležaja                 | 6204ZV                   |

## PERFORMANSE

|                        |           |
|------------------------|-----------|
| Performanse kotrljanja | ● ● ● ● ● |
| Buka u pokretu         | ● ● ● ○ ○ |
| Ishrana                | ● ● ● ● ● |
| otpornost na rdju      | ● ● ● ○ ○ |

## OSNOVNI ATRIBUTI

|                                |          |
|--------------------------------|----------|
| Naziv proizvoda                | Duratech |
| Tip kućišta                    | Tocak    |
| Nosivost na 3 km/h             | 900 kg   |
| Statički Nosivost              | 1800 kg  |
| Temperaturni opseg (Minimalno) | -40 °C   |
| Opseg temperature (maksimalni) | 80 °C    |
| Ukupna težina                  | 0,547 kg |

# DURATECH

TOP082X88-Ø20 HL90

EAN 4031582322613  
Broj porudžbine 00804433



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

