

DURATECH

TOP082X88-Ø20 HL90

EAN 4031582322613

Broj porudžbine 00804433



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid težak
materijal omotaca	Identično sa telom Tocak
Nošenje	precizini kuglicni lezaj
stitnici omotaca	Bez stražara
Prečnik	82 mm
Širina omotac	88 mm
dimenzija rupa osovina	20 mm
dužina glavcine	90 mm
Teškoća gazećeg omotac (D)	75 Šor D
Tip ležaja	6204ZV

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Tip	Tocak
Nosivost na 3 km/h	900 kg
Statički Nosivost	1800 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,547 kg

DURATECH

TOP082X88-Ø20 HL90

EAN 4031582322613

Broj porudžbine 00804433



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

