

# AGILA

2470DIK075R07-Ø24-27

EAN 4031582328134



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement Noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product Name                | Agila                     |
| Type                        | Swivel castor             |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 3 km/h     | 55 kg                     |
| Electric Conductive         | No                        |
| Stainless                   | No                        |
| Load capacity Static        | 110 kg                    |
| Temperature range (Minimum) | -10 °C                    |
| Temperature range (Maximum) | 40 °C                     |
| Overall Height              | 103 mm                    |
| Overall weight              | 0.48 kg                   |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Housing Material    | Steel sheet, medium |
| Fork shape          | Broad               |
| Swivel Bearing      | Two ball races      |
| Housing Color       | Blue passivated     |
| Offset              | 24 mm               |
| Swivel radius       | 61.5 mm             |
| Swivel interference | 123 mm              |

## WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Sheet Steel               |
| Tread Material Mix    | Solid rubber, non-marking |
| Bearing               | Cone ball bearing         |
| Threadguards          | With threadguard          |
| Diameter              | 75 mm                     |
| Tread width           | 25 mm                     |
| Hardness of tread (A) | 80 Shore A                |

## FITTING

|                            |                                                            |
|----------------------------|------------------------------------------------------------|
| Fitting type               | Synthetic expander, round                                  |
| Expander fitting (Minimum) | 24 mm                                                      |
| Expander fitting (Maximum) | 27 mm                                                      |
| Hint                       | Please indicate required tube innerdiameter when ordering. |

# AGILA

2470DIK075R07-Ø24-27

EAN 4031582328134



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

