

PRODUCT INFORMATION

# DURATECH HEAT

IOG 100x35-Ø8,4 clip

EAN 4031582347234



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Aluminum
Tread material	Identical with wheel body
Bearing	Dry bearing bush
Wheel color	Metallic
Threadguards	Without threadguard
Diameter	3.94 in
Tread width	1.38 in
Axle hole diameter	0.33 in
Hub length	1.77 in
Body width	1.38 in
Hardness of tread (D)	95 Shore D

## PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

## CORE ATTRIBUTES

Product name	Duratech heat
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	275.58 lb
Electric conductive	no
Stainless	Yes
Load capacity Static	551.16 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	536 °F
Overall weight	0.75 lb

# DURATECH HEAT

IOG 100x35-Ø8,4 clip

EAN 4031582347234

Order number 00034267  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

