

# ALPHA STAINLESS

8470XSC100P30-13

EAN 4031582381603  
Order number 00062784



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	●●●○○
Movement noise	●●●○○
Attrition	●●●●○
Corrosion resistance	●●●●●

## CORE ATTRIBUTES

Product name	Alpha stainless
Type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	200 kg
Electric conductive	✓
Stainless	✓
Load capacity Static	400 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall height	128 mm
Overall width	75 mm
Overall weight	0.725 kg

## WHEEL

Body material	Polyamide, electric conductive
Tread material	Polyurethane, injected, electric-conductive
Bearing	Precision ball bearing, stainless
Axle	Screwed with nut
Wheel color	Silver grey (similar RAL7001)
Threadguards	With threadguard
Diameter	100 mm
Tread width	36 mm
Body width	36 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

## HOUSING

Material fork	Stainless steel, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Colour	Stainless steel
Offset	41 mm
Swivel radius	91 mm
Swivel interference	182 mm
Dome diameter	75 mm

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	13 mm

# ALPHA STAINLESS

8470XSC100P30-13

EAN 4031582381603  
Order number 00062784



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

