

DURATECH

TOP 085x65-Ø20 HL65

EAN 4031582331172



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	1433 lb
Load capacity at 3.7 mph	1146.4 lb
Electric conductive	no
Stainless	no
Load capacity Static	2866.01 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	1.19 lb

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	3.35 in
Tread width	2.56 in
Axle hole diameter	0.79 in
Hub length	2.56 in
Body width	2.56 in
Hardness of tread (D)	75 Shore D
Bearing type	6204

DURATECH

TOP 085x65-Ø20 HL65

EAN 4031582331172

Order number 00832611

Product Drawings



BETTER MOBILITY. BETTER LIFE.

