

# ALPHA

3478DPR200P63

EAN 4031582439175



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ○ ○ ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Alpha
Type	Fixed castor
Load capacity at 1.8 mph	165.35 lb
Load capacity Static	330.69 lb
Overall height	9.45 in
Overall weight	3.79 lb

## WHEEL

Body material	Sheet Steel
Tread material	Pneumatic tire, line profile
Bearing	Roller bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	7.87 in
Tread width	1.97 in

## HOUSING

Material	Steel sheet, heavy
Fork shape	Broad

## FITTING

Fitting type	Rectangular plate
Plate length	5.39 in
Plate width	4.53 in
Plate hole length (Maximum)	4.13 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	3.15 in
Plate hole diameter	0.43 in

# ALPHA

3478DPR200P63

EAN 4031582439175



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

