

PRODUCT INFORMATION

ELASTECH

UER125x40-Ø15 HL58

EAN 4031582442878



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	551.16 lb
Electric conductive	no
Stainless	no
Load capacity Static	1102.31 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall weight	0.95 lb

WHEEL

Body material	Polyamide
Tread material	Elastic tire, black, vulcanized
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	4.92 in
Tread width	1.57 in
Axle hole diameter	0.59 in
Hub length	2.28 in

