

PRODUCT INFORMATION

MAXTECH

PNR389x85-Ø20 HL74 TFR

EAN 4031582400342



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Polyurethane, foamed
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	15.31 in
Tread width	3.35 in
Axle hole diameter	0.79 in
Hub length	2.91 in

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Load capacity at 1.8 mph	165.35 lb
Electric conductive	no
Stainless	no
Load capacity Static	330.69 lb
Overall weight	4.3 lb

MAXTECH

PNR389x85-Ø20 HL74 TFR

EAN 4031582400342



BETTER MOBILITY. BETTER LIFE.

Product Drawings

