PRODUCT INFORMATION

ELASTECH

UFR 125x40-Ø12 HL44,4 tyre-5015

EAN 4031582323405



Image may differ from the original product

WHEEL

Tread hardness	soft
Body material	Polyamide
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Roller bearing
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	4.92 in
Tread width	1.57 in
Axle hole diameter	0.47 in
Hub length	1.75 in
Body width	1.57 in
Hardness of tread (A)	63 Shore A

PERFORMANCE

Roll Performance	●●●●○
Movement noise	●●●●○
Attrition	●●●○○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	551.16 lb
Electric conductive	no
Stainless	no
Load capacity Static	1102.31 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall weight	0.33 lb

© Copyright 2026 TENTE International GmbH


ELASTECH

UFR 125x40-Ø12 HL44,4 tyre-5015

EAN 4031582323405

Order number 00030734

Product Drawings



© Copyright 2026 TENTE International GmbH