

PRODUCT INFORMATION

MAXTECH

UAD 125x40-Ø20 HL58 natural/5017

EAN 4031582322781



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	661.39 lb
Electric conductive	no
Stainless	Yes
Load capacity Static	1322.77 lb
Temperature range (Minimum)	-13 °F
Temperature range (Maximum)	176 °F
Overall weight	1.12 lb

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Roller bearing, stainless
Wheel color	Natural white
Diameter	4.92 in
Tread width	1.57 in
Axle hole diameter	0.79 in
Hub length	2.28 in
Body width	1.57 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

MAXTECH

UAD 125x40-Ø20 HL58 natural/5017

EAN 4031582322781

Order number 00064271

Product Drawings



BETTER MOBILITY. BETTER LIFE.

