

STYLEA

5923UOI075B10-11X20/10D20 9011/9011

EAN 4031582311075



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ● |
| Corrosion Resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

|                             |                                       |
|-----------------------------|---------------------------------------|
| Product Name                | Stylea                                |
| Type                        | Swivel castor with intermittend brake |
| Standard                    | EN12529 - Swivel Chairs Castors       |
| Load capacity at 3 km/h     | 50 kg                                 |
| Electric Conductive         | No                                    |
| Stainless                   | No                                    |
| Load capacity Static        | 100 kg                                |
| Temperature range (Minimum) | -20 °C                                |
| Temperature range (Maximum) | 60 °C                                 |
| Overall Height              | 77 mm                                 |
| Overall width               | 54 mm                                 |
| Overall weight              | 0.16 kg                               |

HOUSING

|                     |                          |
|---------------------|--------------------------|
| Housing Material    | Polyamide                |
| Fork shape          | Twin wheel housing       |
| Swivel Bearing      | Stem, swiveling          |
| Housing Color       | Graphite black (RAL9011) |
| Offset              | 30 mm                    |
| Swivel radius       | 62 mm                    |
| Swivel interference | 124 mm                   |
| Dome diameter       | 20 mm                    |

WHEEL

|                       |                                |
|-----------------------|--------------------------------|
| Body material         | Polyamide                      |
| Tread Material Mix    | Identical with wheel body      |
| Bearing               | Plain bearing with spacer tube |
| Axle                  | Riveted                        |
| Tread Color           | Graphite black (RAL9011)       |
| Wheel Color           | Graphite black (RAL9011)       |
| Threadguards          | Without threadguard            |
| Diameter              | 75 mm                          |
| Tread width           | 8 mm                           |
| Axle Hole Diameter    | 0 mm                           |
| Hub Length            | 0 mm                           |
| Body width            | 8 mm                           |
| Hardness of tread (D) | 65 Shore D                     |

FITTING

|               |                                  |
|---------------|----------------------------------|
| Fitting type  | Stem with grip ring, with collar |
| Stem diameter | 11 mm                            |
| Stem length   | 20 mm                            |

# STYLEA

5923UOI075B10-11X20/10D20 9011/9011

EAN 4031582311075

Order number 00071010

**Product Drawings**



BETTER MOBILITY. BETTER LIFE.

