

ELASTECH HEAT

IDP100X30-8 HL50

EAN 4031582460667



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Aluminium
Tread material	Damping, heat resistant
Bearing	Precision ball bearing
Threadguards	Without threadguard
Diameter	100 mm
Tread width	30 mm
Axle hole diameter	8 mm
Hub length	50 mm
Hardness of tread (A)	80 Shore A

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ○ ○ ○

CORE ATTRIBUTES

Product name	Elastech heat
Housing type	Wheel
Load capacity at 3 km/h	200 kg
Load capacity Static	400 kg
Temperature range (Minimum)	-30 °C
Temperature range (Maximum)	280 °C
Overall weight	0.294 kg