

NOVATECH

ETP 082X60-Ø20 HL62

EAN 4031582318678
Order number 00801537



BETTER MOBILITY. BETTER LIFE.




Image may differ from the original product

WHEEL

Body material	Steel, iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	82 mm
Tread width	60 mm
Axle hole diameter	20 mm
Hub length	62 mm
Body width	60 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D
Bearing type	6204ZV

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	600 kg
Load capacity at 6 km/h	480 kg
Load capacity Static	1200 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	1.092 kg

NOVATECH

ETP 082X60-Ø20 HL62

EAN 4031582318678
Order number 00801537



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

