

FOOTMASTER

FOOT MASTER GD- 60-S-NYN

EAN 4031582413212



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	○ ○ ○ ○ ○
Buka u pokretu	○ ○ ○ ○ ○
Ishrana	○ ○ ○ ○ ○
otpornost na rdju	○ ○ ○ ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Footmaster
Tip	Okretanje Tocak
Nosivost na 3 km/h	280 kg
Električni provod	no
nerdjajuci	no
Statički Nosivost	280 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	90 °C
Sveukupna visina	82 mm
Ukupna širina	70 mm
Ukupna težina	0.7 kg

KUCISTE

Boja	Beli
ofset	36 mm
okretni radijus	61 mm
Otpor okretanju	122 mm
Prečnik kupole	70 mm

TOCAK

Nošenje	kotrljajuci lezaj, navlažen
Boja Tocak	Crna
Prečnik	50 mm
Širina omotac	25 mm
Širina tela	25 mm

FOOTMASTER

FOOT MASTER GD- 60-S-NYN

EAN 4031582413212

Broj porudžbine 00062140
Product Drawings



BETTER MOBILITY. BETTER LIFE.

