

ELASTECH

EEZ250x60-Ø190 DG

EAN 4031582318340



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Tread hardness	soft
Body material	Steel, iron
Tread material	Elastic tire, black, vulcanized
Bearing	Borehole, unmachined
Diameter	9.84 in
Tread width	2.36 in
Axle hole diameter	7.48 in
Hardness of tread (A)	68 Shore A

PERFORMANCE

Roll Performance	● ● ● ● ○ ○
Movement noise	● ● ● ● ○ ○
Attrition	● ● ● ● ○ ○
Corrosion resistance	● ● ● ● ○ ○

CORE ATTRIBUTES

Product name	Elastech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	1388.91 lb
Load capacity at 3.7 mph	1157.43 lb
Electric conductive	no
Stainless	no
Load capacity Static	2777.82 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall weight	2.99 lb

ELASTECH

EEZ250x60-Ø190 DG


EAN 4031582318340

Order number 00830877

Product Drawings



BETTER MOBILITY. BETTER LIFE.




PRODUCT INFORMATION

ELASTECH

EEZ250x60-Ø190 DG

EAN 4034582318340

Order number 00880877



BETTER MOBILITY. BETTER LIFE.