

PURETECH

PIR080X35-Ø8 HL44,4

EAN 4031582453157



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Solid rubber, non-marking
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	3.15 in
Tread width	1.38 in
Axle hole diameter	0.31 in
Hub length	1.75 in
Hardness of tread (A)	85 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ○ ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	154.32 lb
Load capacity Static	308.65 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.43 lb

PURETECH

PIR080X35-Ø8 HL44,4

EAN 4031582453157



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

